TECHLABSYSTEMS



BURSTING STRENGTH TESTER BT-10 model

For Determining the Bursting Strength Value of Paper and Corrugated Board "Mullen type"

Applicable standards: ISO 2758 / 2759 - SCAN P25/P24 - TAPPI T403 / T807 / 810 -PAPTAC D19P/D8 - BS 3137 - DIN 53141 - AP/AS 1301,403 - ASTM D774







- □ 15" laptop PC interface for Data Acquisition and Control
- LYNX Burst Test Programme
- □ Statistics: Min/Max, Average and Standard Deviation
- □ Save Print Copy to Office Clipboard...
- □ Direct Reading in kPa Kg/cm² Bar & PSI
- USB interface f/connection to a PC
- □ Improve Your Quality System to ISO 9000
- Eliminates Human Error
- □ Languages: (English Spanish German and French)
- □ Measurement ranges: (f/ PAPER: from 0 to 1500 kPa & f/BOARD: from 200 to 5.000 kPa)
- □ Security System of operation included
- Pneumatic Clamping System
- □ Constant Pressure Clamping
- □ Acrylic protection screen (for test area)
- □ It is posible to integrate in:
 - LYNX Management Module with basic statistics (one-to-one connection))
 - Advanced Management Laboratory Software LYNX Plus & Pro (f/multiple test equipment connection)

TECHLAB SYSTEMS, S.L.



TEST DESCRIPTION

Tests are made by means of applying hydraulic pressure (glycerine hydraulic liquid) to the sample by a natural rubber membrane. The maximum pressure reached at the breaking moment of the sample is displayed in the Ultralight PC color monitor (digital and Graphic mode).

After placing the sample in its test position, press the test button in the LYNX software. The acrylic protection screen will go down followed by the pneumatic clamping device to support the sample. The hydraulic pressure will begin to apply underneath the sample automatically. When the sample breaks, the hydraulic cylinder will automatically stop and reverse the movement, until it arrives to its initial test position. The pressure at which the sample breaks will be captured by the LYNX software.

The protection screen and the sample support will be automatically open, leaving the equipment ready for next sample test.

The new model performs burst tests in both **PAPER**, as well as **CORRUGATED BOARD**. The rubber membrane is put in place and the pumping speed specified by the according standard is automatically selected on the front panel.

* CORRUGATED BOARD = 170 +/- 15 ml / min

* **PAPER** = 95 +/- 5 ml / min

SPECIFICATIONS

- □ Measure range from:
 - Paper: from 0 to 1500 kPa
 - Board: from 200 to 5.000 kPa
- □ Accuracy: +/- 1 % of reading between 2 % and 100 % of full scale
- □ Selecting the breaking detection level between 10% and 90% of maximum value
- □ Reading in a monitor of 8,9 ":
 - kPa resolution to 0.2 kPa
 - Bars resolution to 0.002 Bar
 - Kg/cm^2 resolution to 0.002 Kg / cm^2
 - PSI resolution to 0.03 PSI
- □ Statistics: minimum & maximum values, average and standard deviation
- □ Automatic test cycle with breaking detection and auto-return to initial test position
- Maximum value memory
- Manual and automatic reset
- □ Select flow of pumping speed by keyboard: 170 ml / min. (corrugated board) and 95 +/- 5 ml / min. (paper)
- □ With data output by USB
- □ Maximum thickness of sample: 12 mm
- □ Sample clamping strength of 7000 N max., adjustable by pneumatic regulator
- Methacrylate protection screen (tests area)
- Emergency switch
- Glycerine deposit store of 200 cc capacity, facilitating a easy drain of the air out of the system
- □ Air consumption: 0,6 l/test

NOTE: Upon ordering, indicate the burst tester model : Paper or Corrugated Board

CONNECTIONS:		DELIVERY CONTENT:
Electrical: 110	//60Hz or 230V/50Hz single-phase	> Burst Strength Tester BT-10 model
Compressed Air:	600 kPa	>15" laptop PC with Windows OS
		> LYNX Burst Testing Software
		> 1 set of grips to test Paper or Corrugated Board with 1membrane
DIMENSIONS AND WEIGHT:		> 1 set of keys to perform membrane changes.
Dimensions:	400 x 550 x 550 mm (W x D x H)	> 500 ml glycerine
Box for transport:	500 x 650 x 650 mm (W x D x H)	
Weight Net/Gross:	65 Kg /110 Kg	

* TECHLAB SYSTEMS reserves the right to do any technical modification without advance notice

Doc. : BT10-1-CAT-E-R2





"Data in Real Time..."

LYNX Test Programme for BURST RESISTANCE with "Mullen" index calculations - B.E.A. (Burst Energy Absorption) and Pressure.

	Colour Pa KPa Zero Max Setup	vameters Results Returns Help	cm3 Zero
Current Sample Calculus 2 b.e.a. 971.23 burst index 767.9 pressure 767.9	2,000 1,800 1,800 1,000 1,000 1,000 0 1,000 0 0 1,000 0 0 1 200 0 0 1 200	3 4 5 Volume (cm3)	Sample1


"Mullen" Index (kN/g, kPa.m²/g)

Burst Resistance (kPa, PSI, Bar Kg/cm²)

- Quickness in carrying out tests and in obtaining results.
- No human mistakes.
- Traceability according to ISO 9000
- It marks Maximum - Minimum - Medium Value and Standard Deflection
- Up to 100 Tests or Measurement Capacity for each report
- SAVE – PRINT and COPY to OFFICE CLIPBOARD FUNCTIONS

OPTIONAL : LYNX MANAGEMENT MODULE with Basic Statistics

If you need to manage the data generated, we recommend the purchase of this module which allows further choice of language, reporting, to have a library of units, levels of password, introduction of minimum values, maximum and optimal to exploit data with statistics, charts bars, Bells of GAUSS, Comparison tolerances ..., export data to Word - Excel ..., PDF generation ...



* TECHLAB SYSTEMS reserves the right to do any technical modification without advance notice

Doc. : LYNX_Burst-1-CAT-I-R1

TECHLAB SYSTEMS, S.L. Head Office: Txatxamendi 10, Pol. 110 – 20100 Lezo – SPAIN

US Office: 1549 Ardmore Ave. –Itasca, Illinois 60143 USA www.techlabsystems.com